

[See all 7 Products in Family](#)

4 Watt, 230V, 365nm UV Curing Lamp



Stock **#86-801** **3 In Stock**

- 1 + **A\$412⁸⁰**

ADD TO CART

Volume Pricing	
Qty 1+	A\$412.80 each
Need More?	Request Quote

Product Downloads

General

Note:

Voltage converter required for use in U.S.

Optical Properties

Wavelength (nm):	
365.00	
Irradiance at 76.2mm (μW/cm²):	
1300	

Hardware & Interface Connectivity

4W, 230V	Power Requirement:
----------	--------------------

Regulatory Compliance

View	Certificate of Conformance:
----------------------	-----------------------------

Product Details

Stands are not included, but recommended for hands free curing or analysis.

- 4-Watt and 6-Watt Models Centered at 365nm
- Stands are Available for Hands Free Curing
- Portable, High Intensity Design

Handheld UV Curing Lamps are portable benchtop lamps designed for a variety of applications including the fluorescence of stained gels, sterilization, or UV curing. These lamps feature ergonomically designed handles with conveniently placed on/off switches. These lamps are portable, with a high-intensity design. Handheld UV Curing Lamps are ideal for quickly curing Edmund Optics' full line of [Norland Optical Adhesives](#). These lamps are available in 4-watt and 6-watt models centered at 365nm.

Note: Stands are not included, but are recommended for hands free curing or analysis.