

4" x 4" 940nm Edge-Lit Backlight

See More by [Advanced Illumination](#)



Stock #73-908 NEW 1 In Stock

-

1

+

A\$1,304⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$1,304.00 each
Need More?	Request Quote

Product Downloads

General	
BX2-100100940IC	Model Number:
50,000	LED Lifetime (hours):
LED Illuminator	Type of Illumination:
Advanced Illumination	Manufacturer:
Backlight	Geometry:

Constant	Illumination Mode:
Physical & Mechanical Properties	
157.5 L x 157.5 W x 19.1 T	Dimensions (mm):
4 x 4	Active Area (inches):
Optical Properties	
NIR	Color:
940	Wavelength (nm):
Hardware & Interface Connectivity	
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855	
Environmental & Durability Factors	
0 - 35	Operating Temperature (°C):
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:

Product Details

- 30% Brighter than Comparable Surface Mount Light
- Uniform, Low Heat Illumination

Advanced Illumination Side-Fired LED Backlights are high performance alternatives to surface mount lights. Advanced Illumination Side-Fired LED Backlights provide uniform, low heat illumination that is 30% brighter than surface mount lights of equal size. To simplify system integration, these backlights include mounting brackets and mounting channels for M6 nuts.

Note: Required 24V power supply [#66-855](#). [Accessories for Advanced Illumination products](#) are available and sold separately. Units cannot be intensity controlled.