

4.0 OD M55 x 0.75, Machine Vision Absorptive ND Filter



Stock #21-501

3-5 DAYS

-

1

+

A\$190.40

ADD TO CART

Qty 1-9

A\$190.40

Qty 10+

A\$181.44

Volume Pricing

[Request Quote](#)

Get Product Downloads

Optical Density OD (Average):
4.0

Clear Aperture CA (mm):
50.00

Filter Thread:
M55 x0.75

Substrate:
ND Filter Glass

Surface Quality: 40-20
Transmission (%): 0.01
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
