

## 4.0 OD M72 x 0.75, Machine Vision Absorptive ND Filter



Stock #21-603 3-5 DAYS

- 1 + **A\$300.80**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| A\$300.80                     |
| Qty 10+                       |
| A\$285.44                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads

Optical Density OD (Average):  
4.0

Clear Aperture CA (mm):  
67.50

Filter Thread:  
M72 x0.75

Substrate: ☐  
ND Filter Glass

|                                                       |
|-------------------------------------------------------|
| <b>Surface Quality:</b><br>40-20                      |
| <b>Transmission (%)</b> :<br>0.01                     |
| <b>Type:</b><br>Mounted Imaging Filter                |
| <b>Blocking Wavelength Range (nm):</b><br>425 - 675   |
| <b>Mount Thickness (mm):</b><br>6.0                   |
| <b>Mount Thickness Including Threads (mm):</b><br>8.3 |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |

---