

TECHSPEC® 400-700nm OD 2.5, M30.5 x 0.5 Absorptive ND Filter



Stock #66-727

3-5 DAYS

-

1

+

A\$124.80

ADD TO CART

Qty 1-9

A\$124.80

Qty 10+

A\$116.48

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
33.50

Optical Density OD (Average):
2.5

Clear Aperture CA (mm):
22.0

Filter Thread:
M30.5 x 0.50

Substrate: ND Filter Glass
Coating: Uncoated
Transmission (%): 0.30
Type: Neutral Density Filter
Stock No. of Unmounted Filter: #46-216
Mount Thickness (mm): 9.2
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View