

405nm Single Stage Free-Space Optical Isolator



405nm Single Stage Free-Space Optical Isolator, #35-969

Stock **#35-969**

3-5 DAYS

-

1

+

A\$3,721.60

ADD TO CART

|                               |
|-------------------------------|
| Qty 1+                        |
| A\$3,721.60                   |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads

|                                           |
|-------------------------------------------|
| Clear Aperture CA (mm):<br>4.7            |
| Design Wavelength DWL (nm):<br>405        |
| Minimum Transmission (%):<br>85           |
| Operating Temperature (°C):<br>+15 to +40 |
| Transmission (%):<br>92 (typical)         |

|                                                                                                  |
|--------------------------------------------------------------------------------------------------|
| <b>Type:</b><br>Single Stage Optical Isolator                                                    |
| <b>Wavelength Range (nm):</b><br>395 - 425                                                       |
| <b>Style:</b><br>Faraday                                                                         |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>40 W, 4 kW/cm <sup>2</sup> @ DVL |
| <b>Typical Isolation at Design Wavelength (dB):</b><br>43                                        |
| <b>Minimum Isolation at Design Wavelength (dB):</b><br>38                                        |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |