

406 x 406mm, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock **#85-206** 3-5 DAYS

⊖ 1 ⊕ **A\$436.80**

ADD TO CART

Qty 1-5

A\$436.80

Qty 6+

A\$349.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
80-50

Dimensions (mm):

406.0 x 406.0 ±0.76
Coating Specification: R _{avg} >85% @ 400 - 700nm
Coating: Protected Aluminum (400-700nm)
Coating Type: Metal
Angle of Incidence (°): 45.00
Bevel: Protective as needed
Clear Aperture (%): >90
Thickness (mm): 6.00
Type: Flat Mirror
Wavelength Range (nm): 400 - 700
Length (mm): 406.00
Width (mm): 406.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant