

40° Travel, 40 x 40mm Stage Size Metric Goniometer, R47



Stock #55-838 3-5 DAYS

- 1 +

A\$1,006.40

ADD TO CART

Qty 1-4
A\$1,006.40
Qty 5+
A\$905.76
Volume Pricing
Request Quote

Get Product Downloads

Type of Movement:
Goniometer

Guide System:
Dovetail

Type of Drive:
Lead Screw

Type:
Metric

Stage Size (mm): 40 x 40
Travel (°): ±20
Construction: Brass Stage
Load Capacity (kg): 3
Mounting Threads: (1) M4 x 0.7, (4) M3 x 0.5, (4) M2 x 0.4
Radius R (mm): 47
Resolution (°): 0.2
Weight (kg): 0.2

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
