

40mm Sq. English Kinematic Magnetic Base



Stock #22-407 **7 In Stock**

⊖ 1 ⊕ A\$174⁰⁰

ADD TO CART

Volume Pricing

Qty 1-9	A\$174.40 each
Qty 10+	A\$158.08 each
Need More?	Request Quote

Product Downloads

General

English **Type:**

No **Switchable:**

Physical & Mechanical Properties

40.00 **Length (mm):**

40.00 **Width (mm):**

25.40 **Thickness (mm):**

Anodized Aluminum **Construction:**

0.08 **Weight (kg):**

<70.0 **Repeatability (µrad):**

Threading & Mounting

Mounting Threads:
(4) 2-56, (4) 6-32, (2) 8-32, (1) 1/4-20

Material Properties

10 **Magnetic Force (N):**

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 247:
[Compliant](#)

Product Details

- Common 25.4mm (1") Platform Height
- Removable Top Plates with High Repeatability Kinematic Positioning
- Compatible with all with [TECHSPEC Stages](#)

Kinematic Magnetic Base Plates are ideal for simplifying the adjustment of subsystems in a benchtop optical system. The bases feature a common platform height of 25.4mm (1") to allow for simplified optical axis alignment. Each base has a removeable top plate, ideal for adding or removing system components and subassemblies anywhere on a lab table with ease. Internal kinematic positioning allows the top plates to be removed and replaced with high repeatability. Kinematic Magnetic Base Plates are directly compatible with our [TECHSPEC stages](#), making them an ideal lab bench component for system building.