

TECHSPEC[®] 40mm, Center Drive, Standard Top, Metric Stage



40mm, 0.5" Travel, Lead Screw Drive Stage (Center Drive)

Stock #66-408 3-5 DAYS



1



A\$516.80

ADD TO CART

Qty 1-2

A\$516.80

Qty 3+

A\$451.04

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:

Linear (X)

Guide System:

Crossed Roller Bearing

Type of Drive:

Lead Screw

Drive Orientation:

Center Drive
Type: Metric
Stage Size (mm): 40 x 40
Travel (mm): 13
Center Hole: M6 x 1
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 4
Mounting Threads: (1) M6 x 1, (4) M3 x 0.5, (8) M2 x 0.4
Stage Size (inches): 1.57 x 1.57
Straight Line Accuracy (µm): 2
Pitch (arcsec): 30
Yaw (arcsec): 25

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant