

TECHSPEC® 4.0mm Diameter, Fused Silica Half-Ball Lens



Stock #67-396 3-5 DAYS

- 1 +

A\$80.80

ADD TO CART

Qty 1-10
A\$80.80
Qty 11+
A\$64.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
4.00

Substrate:
[Fused Silica](#) (Corning 7980)

Coating:
Uncoated

Type:

Half-Ball Lens
Wavelength Range (nm): 200 - 2200
Index of Refraction n_d: 1.458
Radius R (mm): 2.00
Radius Tolerance (μm): ± 2.5
Sphericity (μm): 0.625
Thickness Tolerance (μm): ± 35
Diameter Tolerance (μm): ± 2.5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant
