

28mm Max. Aperture, Stainless Steel Iris Diaphragm



Stock #64-504 3-5 DAYS

- 1 + **A\$144.00**

ADD TO CART

Qty 1-4
A\$144.00
Qty 5+
A\$127.52
Volume Pricing
Request Quote

Get Product Downloads

Type: Unmounted
Minimum Aperture (mm): 1.5
Maximum Aperture (mm): 28.0
Outer Diameter (mm): 40.0

Construction: Blackened Brass Housing, Stainless Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 12.60
Number of Leaves: 16.00
Thickness (mm): 5.50

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)