

40mm Precision Stage, English Dovetail Carrier



40mm Precision Stage, English Dovetail Carrier

Stock #12-510 3-5 DAYS



1



A\$188.80

ADD TO CART

Qty 1-9

A\$188.80

Qty 10+

A\$167.04

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:

Linear (X)

Guide System:

Dovetail

Type of Drive:

Manual

Type:

English
Length (inches): 1.57
Length (mm): 40.00
Construction: Black Anodized Aluminum
Mounting Threads: (4) 6-32, (8) 2-56, (1) 1/4-20
Note: Carrier

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant