

**TECHSPEC® 40mm, Side Drive, Standard Top, English Stage**



40mm, Side Drive, Solid Top Stage

Stock **#66-405** **3 In Stock**

⊖ 1 ⊕ **A\$625<sup>00</sup>**

**ADD TO CART**

Volume Pricing

Qty 1-2	<b>A\$625.60</b> each
Qty 3+	<b>A\$546.24</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

English **Type:**

**Physical & Mechanical Properties**

Linear (X) **Type of Movement:**

Crossed Roller Bearing **Guide System:**

**Drive Orientation:**



**30mm Standard-Top Stages - Center Drive**



**30mm Standard-Top Stages - Side Drive**



**40mm Standard-Top Stages - Center Drive**



**40mm Standard-Top Stages - Side Drive**



**70mm Standard-Top Stages - Center Drive**



**70mm Standard-Top Stages - Side Drive**



**125mm Standard-Top Stages - Center Drive**



**125mm Standard-Top Stages - Side Drive**

