

TECHSPEC[®] 40mm, Side Drive, Standard Top, English Stage



40mm, Side Drive, Solid Top Stage

Stock **#66-405** **3 In Stock**

-

1

+

A\$625⁶⁰

ADD TO CART

Volume Pricing	
Qty 1-2	A\$625.60 each
Qty 3+	A\$546.24 each
Need More?	Request Quote

Product Downloads

General

Type:

English

Physical & Mechanical Properties

Type of Movement:

Linear (X)

Guide System:

Crossed Roller Bearing

Drive Orientation:



30mm Standard-Top Stages - Center Drive



30mm Standard-Top Stages - Side Drive



40mm Standard-Top Stages - Center Drive



40mm Standard-Top Stages - Side Drive



70mm Standard-Top Stages - Center Drive



70mm Standard-Top Stages - Side Drive



125mm Standard-Top Stages - Center Drive



125mm Standard-Top Stages - Side Drive

