

[See all 60 Products in Family](#)

**TECHSPEC® 40mm, Side Drive, Standard Top, Metric Extended Micrometer**



TECHSPEC® Crossed-Roller Bearing Linear Translation Stages (Standard-Top Model)



Stock #66-413 [CONTACT US](#)

⊖ 1 ⊕ A\$736<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-2	A\$736.00 each
Qty 3+	A\$642.56 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Metric **Type:**

**Physical & Mechanical Properties**

Linear (X) **Type of Movement:**

**Guide System:**



**30mm Standard-Top Stages - Center Drive**



**30mm Standard-Top Stages - Side Drive**



**40mm Standard-Top Stages - Center Drive**



**40mm Standard-Top Stages - Side Drive**



**70mm Standard-Top Stages - Center Drive**



**70mm Standard-Top Stages - Side Drive**



**125mm Standard-Top Stages - Center Drive**



**125mm Standard-Top Stages - Side Drive**

