

[See all 6 Products in Family](#)

40mm Sq. English Kinematic Magnetic Base



Stock **#22-407** 9 In Stock

-

1

+

A\$174^{.40}

ADD TO CART

Volume Pricing	
Qty 1-9	A\$174.40 each
Qty 10+	A\$158.08 each
Need More?	Request Quote

Product Downloads

General	
English	Type:
No	Switchable:
Physical & Mechanical Properties	
25.40	Thickness (mm):
40.00	Width (mm):

0.08	Weight (kg):
Anodized Aluminum	Construction:
40.00	Length (mm):
<70.0	Repeatability (μrad):

Threading & Mounting

(4) 2-56, (4) 6-32, (2) 8-32, (1) 1/4-20	Mounting Threads:
--	-------------------

Material Properties

10	Magnetic Force (N):
----	---------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Common 25.4mm (1") Platform Height
- Removable Top Plates with High Repeatability Kinematic Positioning
- Compatible with all with [TECHSPEC Stages](#)

Kinematic Magnetic Base Plates are ideal for simplifying the adjustment of subsystems in a benchtop optical system. The bases feature a common platform height of 25.4mm (1") to allow for simplified optical axis alignment. Each base has a removeable top plate, ideal for adding or removing system components and subassemblies anywhere on a lab table with ease. Internal kinematic positioning allows the top plates to be removed and replaced with high repeatability. Kinematic Magnetic Base Plates are directly compatible with our [TECHSPEC stages](#), making them an ideal lab bench component for system building.