

40mm Sq. Metric Kinematic Magnetic Base



#22-406: 40mm Sq. Metric Kinematic Magnetic Base

Stock **#22-406** 4 In Stock

-

1

+

A\$174⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-9	A\$174.40 each
Qty 10+	A\$158.08 each
Need More?	Request Quote

Product Downloads

General	
Metric	Type:
No	Switchable:

Physical & Mechanical Properties	
25.40	Thickness (mm):
	Width (mm):

40.00	
0.08	Weight (kg):
Anodized Aluminum	Construction:
40.00	Length (mm):
<70.0	Repeatability (μrad):

Threading & Mounting

(4) M2 x0.4, (4) M3 x0.5, (2) M4 x0.7 (1) M6 x1.0	Mounting Threads:
---	-------------------

Material Properties

10	Magnetic Force (N):
----	---------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Common 25.4mm (1") Platform Height
- Removable Top Plates with High Repeatability Kinematic Positioning
- Compatible with all with [TECHSPEC Stages](#)

Kinematic Magnetic Base Plates are ideal for simplifying the adjustment of subsystems in a benchtop optical system. The bases feature a common platform height of 25.4mm (1") to allow for simplified optical axis alignment. Each base has a removeable top plate, ideal for adding or removing system components and subassemblies anywhere on a lab table with ease. Internal kinematic positioning allows the top plates to be removed and replaced with high repeatability. Kinematic Magnetic Base Plates are directly compatible with our [TECHSPEC stages](#), making them an ideal lab bench component for system building.