

## 41mm Diameter Float Glass Window



Stock #02-207 **20+ In Stock**

- 1 + A\$36.<sup>80</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-5	A\$36.80 each
Qty 6-49	A\$33.60 each
Qty 50-99	A\$32.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Protective Window **Type:**  
Glass **Type of Window:**

#### Physical & Mechanical Properties

41.00 **Diameter (mm):**

2.30 **Thickness (mm):**

Fine Ground **Edges:**

## Optical Properties

Uncoated **Coating:**

Float Glass **Substrate:** □

80-50 **Surface Quality:**

350 - 2000 **Wavelength Range (nm):**

4 - 6λ **Surface Flatness (P-V):**

## Regulatory Compliance

**Compliant** **RoHS 2015:**

**View** **Certificate of Conformance:**

**Compliant** **Reach 247:**

## Product Details

- Transmits Visible and Near Infrared Wavelengths
- Available Uncoated or with an Anti-Reflection Coating
- Variety of Sizes Available

Float Glass Optical Windows are optical glass with polished faces that are relatively parallel and are typically used as a protective element between two environments. Float glass readily transmits visible and near-infrared wavelengths and can be used in a wide variety of applications. Float Glass Optical Windows are versatile products offered in circular and rectangular options. They are available uncoated or with BBAR (Broadband Anti-Reflective) 400-700nm coating.

## Compatible Mounts