

108.0mm/4.25" Optic Dia., Optical Cell Kinematic Mount



Stock #57-872 3-5 DAYS

-

1

+

A\$1,396.80

ADD TO CART

Qty 1-9
A\$1,396.80
Qty 10+
A\$1,228.32
Volume Pricing
Request Quote

Get Product Downloads

Type:
Adjustable - Tip-Tilt

Type of Optics:
Circular

Size of Compatible Optics (mm):
108.0

Clear Aperture CA (inches): 4.06 (#57-871)
Clear Aperture CA (mm): 103.1 (#57-871)
Optical Centerline (mm): 85.9
Range: 5°
Dimensions (inches): 5.75 x 3.00 x 6.25
Dimensions (mm): 146.1 x 76.2 x 158.8
Weight (lbs): 3.0
Inner Diameter (inches): 4.625 x 20 TPI
Construction: Black Anodized Aluminum, Stainless Steel
Diameter of Compatible Optics (inches): 4.25
Optical Centerline (inches): 3.38
Optic Holding Style: #57-871 Required
Max. Thickness of Compatible Optics (mm): 22.0 (#57-871)
Adjustment Screw Pitch (inches): 0.015

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View