

## 45° Full Fan Angle Laser Line Generator Lens



Powell Lenses

Stock #43-474 3-5 DAYS



1



A\$372.80

ADD TO CART

Qty 1-5

A\$372.80

Qty 6+

A\$298.40

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):  
8.90 +0.00/-0.15

Substrate: ☐  
[N-SF6](#)

Coating:  
VIS-NIR (450-900nm)

Type:

|                                                       |
|-------------------------------------------------------|
| Beam Shaping Lens                                     |
| <b>Wavelength Range (nm):</b><br>450 - 900            |
| <b>Coating Specification:</b><br>BBAR @ 450 - 900nm   |
| <b>Height (mm):</b><br>8.90 +0.00/-2.00               |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.805 |
| <b>Fan Angle (°):</b><br>45.00                        |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 224:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |