

TECHSPEC[®] 45° AOI, 12.5mm Diameter, Hot Mirror



TECHSPEC High Performance Hot Mirrors

Stock #64-463 3-5 DAYS



1



A\$72.00

ADD TO CART

Qty 1-9

A\$72.00

Qty 10+

A\$62.72

Volume Pricing

[Request Quote](#)

Get Product Downloads

Angle of Incidence (°):

45

Coating:

Hot Mirror, 45°

Diameter (mm):

12.50

Substrate:

[BOROFLOAT®](#)

Surface Quality:
80-50

Thickness (mm):
1.10

Thickness Tolerance (mm):
±0.2

Type:
Dichroic Filter

Dimensional Tolerance (mm):
+0.0/-0.2

Coating Specification:
T_{avg} >85% @ 400 - 690nm, R_{avg} >95% @ 750 - 1125nm
AR: R_{avg} <1% @ 400 - 700nm

Wavelength Range (nm):
400 - 1125

Surface Flatness (P-V):
4 - 6λ

Coating Type:
Dielectric

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)
