

[See all 5 Products in Family](#)

TECHSPEC[®]

45° Tip/Tilt Mount for 25/25.4mm Mirror



#85-696

Stock **#85-696** 3 In Stock

-

1

+

A\$313⁶⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$313.60 each
Need More?	Request Quote

Product Downloads

General	
Tip-Tilt	Function:
Circular	Type of Optics:
Note: Accepts 25/25.4mm Diameter Optics Mounted at 45°	
Physical & Mechanical Properties	
25.0	Compatible Plate Inner Diameter (mm):

Black Anodized Aluminum	Construction:
10 & 12 (Dual Path)	Through Hole Diameter (mm):
25 Dia.	Dimensions (mm):
0.5	Adjustment Screw Pitch (mm):
±8 Tip/Tilt	Travel (°):
Threading & Mounting	
25.0 - 25.4	Size of Compatible Optics (mm):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Available for a Range of Optical Components
- Anodized Aluminum Construction with Stainless Steel Screws
- 0.5mm Pitch Fine Adjustment Screw
- [Fixed Optical Mounts](#) Also Available

Ideal for beam steering applications, TECHSPEC® Cage System Adjustable Optical Mounts are used to integrate a variety of optical components into a TECHSPEC Cage System. Designed to fit within the inner diameter of 25mm or 30mm standard [cage system plates](#), these optical mounts utilize set screws to secure optical components in place, providing the stability and adjustment needed for precision optical alignment. [#85-695](#) 25.4mm Kinematic Mount features a 12.7mm clear aperture and can be paired with [#85-699](#) 45° plate beamsplitter mount.