

45mm Dia. x 32mm FL, Aspheric Condenser Lens



Stock **#19-522** 3-5 DAYS

[Other Coating Options](#)

- 1 +

A\$96.00

ADD TO CART

Qty 1-10
A\$96.00
Qty 11+
A\$86.40
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
45.00 +0.0/-0.2

Effective Focal Length EFL (mm):
32.00

Numerical Aperture NA:
0.70

Back Focal Length BFL (mm):

20.9
Substrate: H-K51
Focal Length Tolerance (%) : ±5
Coating: Uncoated
Centering (arcmin): ≤30
Surface Quality: 80-50 (typical)
Clear Aperture CA (mm): 40.5
Edge Thickness ET (mm): 2.18
Center Thickness CT (mm): 18.50 ±0.30
f#: 0.71
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 45
Radius R₂ (mm): 130
Shape of Back Surface: Convex
Type: Condenser Lens
Wavelength Range (nm): 350 - 2000
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View