

4mm 2 MegaPixel Fixed Focal Length Lens



4mm Fixed Focal Length, #14-394

Stock #14-394 3-5 DAYS

-

1

+

A\$848.00

ADD TO CART

Qty 1+

A\$848.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Iris Option:
Variable

Length (mm):
35.97

Horizontal Field of View, 1/2" Sensor:
77.4°

Maximum Diameter (mm):
44.5

Weight (g):
130

Horizontal Field of View, 1/3" Sensor: 61.93°
Maximum Image Circle (mm): 8.00
Horizontal Field of View @ Max Sensor Format: 77.4°
Type: Fixed Focal Length Lens
Focal Length FL (mm): 4.00
Maximum Sensor Format: 1/2"
Working Distance (mm): 100 - ∞
Mount: C-Mount
Aperture (f/#): f/2 - f/16
Distortion (%): <-2.8
Horizontal Field of View, 1/4" Sensor: 43.6°
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View