


TECHSPEC®

4mm Aperture x 100mm L Low NA, Fused Silica Light Pipe



Fused Silica Light Pipe Homogenizing Rods



Stock #65-831 3-5 DAYS

-

1

+

A\$308.00

ADD TO CART

Qty 1-5

A\$308.00

Qty 6+

A\$246.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Coating:

Uncoated

Substrate:

[Fused Silica](#) (Corning 7980)

Length (mm): 100.00
Surface Quality: 60-40
Type: Light Pipe
Entrance and Exit Aperture (mm): 4.00
Parallelism (arcmin): 5.00
Length Tolerance (mm): ±0.3
Aperture Tolerance (mm): ±0.10
Image Orientation: Light Homogenization
Light Source NA: Low
Wavelength Range (nm): 200 - 2200
Surface Flatness (P-V): 1λ
#Sorting: 25.00

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View