

4μm λ/2 MWIR Zero Order Waveplate



Stock #85-118 3-5 DAYS

-

1

+

A\$1,488.00

ADD TO CART

Qty 1-9
A\$1,488.00
Qty 10+
A\$1,352.00
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):
10.0

Design Wavelength DWL (nm):
4000

Diameter (mm):
25.40

Substrate: ☐
MgF₂

Retardance: λ/2
Type: Crystalline Waveplate
Parallelism (arcmin): 3
Construction: Crystalline
Transmitted Wavefront, P-V: <λ/8 @ 632.8nm
Retardance Tolerance: λ/100 @ 20°C
Mount Thickness (mm): 6.0
Retardance Order: 0

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant