

TECHSPEC[®] 4" Dia. Enhanced Aluminum, $\lambda/10$ Flat ZERODUR[®]



Stock #31-392-533 [CONTACT US](#)

-

1

+

A\$1,544.00

ADD TO CART

Qty 1-5
A\$1,544.00
Qty 6+
A\$1,390.40
Volume Pricing
Request Quote

Get Product Downloads



Surface Flatness (P-V):
 $\lambda/10$ (measured before coating)

Back Surface:
Commercial Polish

Surface Quality: 60-40
Diameter (mm): 101.60 +0.0/-1.0
Substrate: 
Coating Specification: R _{avg} >95% @450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Clear Aperture CA (mm): 91.44
Note: Flatness is specified as Peak to Valley
Thickness (mm): 19.10 ±1.5
Thickness Tolerance (mm): ±1.5
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference:  0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant