

4X Objective, Nikon CFI Plan Fluor

See More by [Nikon](#)



4X Objective, Nikon CFI Plan Fluor, #88-378

Stock **#88-378** 3-5 DAYS

- 1 +

A\$891.20

ADD TO CART

Qty 1+

A\$891.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Compatible Cover Glass Thickness (mm):
N/A

Field of View (mm):
6.25

Horizontal Field of View, 1/2" Sensor:
1.60mm

Horizontal Field of View, 2/3" Sensor:
2.20mm

Model Number:

MRH00045
Length excluding Threads (mm): 42.70
Magnification: 4X
Maximum Diameter (mm): 30
Maximum Sensor Format: 2/3"
Numerical Aperture NA: 0.13
Mounting Threads: M25 x0.75
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Working Distance (mm): 17.2
Weight (g): 140.00
Style: Infinity Corrected
Manufacturer: Nikon
Field Number (mm): 25
Parfocal Length (mm): 59.9
Immersion Liquid: N/A

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Contains SVHC(s)