


50 x 50mm, 0.5mm Spacing, Glass Distortion Target



Stock #58-536 3-5 DAYS

1

A\$1,088.00

ADD TO CART

Qty 1-4
A\$1,088.00
Qty 5+
A\$1,034.24
Volume Pricing
Request Quote

Get Product Downloads

Coating:
Reflective First Surface Chromium
R_{abs} = 50% ±5% @ 550nm

Dot Diameter (mm):
0.250

Dot Spacing (mm):

0.500
Substrate: Soda Lime Float Glass
Optical Density OD (Average): >3.0
Overall Accuracy (mm): ±0.002
Pattern Size (mm): 50 x 50
Dimensions (inches): 3 x 3
Surface Quality: 40-20
Thickness (mm): 1.50
Type: Chrome on Glass
Dot Diameter Tolerance (mm): ± 0.002
Dot Spacing Tolerance (mm): ± 0.002 Center to Center
NIST Certification: Serialized NIST Traceable Certificate Included
Flatness (inches): 0.001

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View
