

TECHSPEC® 50.0mm Dia. x 100.0mm FL, Uncoated, Plano-Convex Lens



Stock **#32-972** 3-5 DAYS

[Other Coating Options](#)



1



A\$68.80

ADD TO CART

Qty 1-9
A\$68.80
Qty 10+
A\$62.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
50.00 +0.0/-0.025

Effective Focal Length EFL (mm):
100.00 @587.6nm

Back Focal Length BFL (mm): 93.41
Coating: Uncoated
Substrate:  N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 10.00 ±0.10
Edge Thickness ET (mm): 3.55
Radius R₁ (mm): 51.68
Clear Aperture CA (mm): 49
f#: 2
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View