

TECHSPEC® 50.0mm Dia. x 50.0mm FL, Uncoated, Plano-Convex Lens



Stock **#32-970** 3-5 DAYS

[Other Coating Options](#)



1



A\$76.00

ADD TO CART

Qty 1-9

A\$76.00

Qty 10+

A\$68.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
50.00 +0.0/-0.025

Effective Focal Length EFL (mm):
50.00 @ 587.6nm

Back Focal Length BFL (mm): 43.28
Coating: Uncoated
Substrate: 
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 12.00 ±0.10
Edge Thickness ET (mm): 3.00
Radius R₁ (mm): 39.24
Clear Aperture CA (mm): 49
f#: 1
Numerical Aperture NA: 0.50
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 2500

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View