

50.0mm FL, No IR-Cut Filter, f/2.5, Micro Video Lens



Stock **#59-781** 3-5 DAYS

- 1 +

A\$118.40

ADD TO CART

Qty 1-49
A\$118.40
Qty 50+
A\$91.20
Volume Pricing
Request Quote

Get Product Downloads

Length (mm):
52.80

Filter Thread:
M12 x 0.50

Maximum Diameter (mm):
27.0

Maximum Image Circle (mm):
8.00

Horizontal Field of View @ Max Sensor Format: 6.8
Resolution, On-Axis: 160 lp/mm @20% Contrast
Resolution, 0.7 Field: 100 lp/mm @20% Contrast
Resolution, Full Field: 80 lp/mm @20% Contrast
Note: Standard
Type: M12 Imaging Lens
Focal Length FL (mm): 50.00
Maximum Sensor Format: 1/2"
Working Distance (mm): 400 - ∞
Mount: M12 x0.5 (S-Mbunt)
Aperture (f/#): f/2.5
Distortion (%): -1.20 @ Full Field
IR Cut Filter: No
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View