


50/50.8mm Dia., Kinematic Mount, 3-Screws, Quick Start Optical Mounts



50/50.8mm Diameter Kinematic Mount, 3-Screws , #58-855



Stock **#17-524** [CONTACT US](#)

-

1

+

A\$307.68

ADD TO CART

Qty 1+

A\$307.68

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type:  
Adjustable - Tip-Tilt

Type of Optics:  
Circular

Size of Compatible Optics (mm):  
50.0 - 50.8

Number of Adjustment Screws:  
3

|                                                                                                        |
|--------------------------------------------------------------------------------------------------------|
| <b>Clear Aperture CA (mm):</b><br>45.9                                                                 |
| <b>Travel (mm):</b><br>Z-Axis: 12                                                                      |
| <b>Construction:</b><br>Aluminum Plates, Stainless Steel Screws, and Brass Thread Bushings             |
| <b>Angle Tolerance (°):</b><br>0.2 per 0.25mm turn                                                     |
| <b>Fine Tilt Angle (°):</b><br>±5                                                                      |
| <b>Fine Tip Angle (°):</b><br>±5                                                                       |
| <b>Sensitivity per 1° Knob Rotation (arcsec):</b><br>2.3                                               |
| <b>Thermal Stability (μrad):</b><br><5                                                                 |
| <b>Adjustment Screw Pitch (mm):</b><br>0.25                                                            |
| <b>Contents of Kit:</b><br><a href="#">#58-855</a> , <a href="#">#15-857</a> , <a href="#">#15-845</a> |
| <b>Compatible Post:</b><br>M4 x0.7, 8-32                                                               |
| <b>Min. Thickness of Compatible Optics (mm):</b><br>2.0                                                |
| <b>Pointing Stability (μrad):</b><br>1.3                                                               |
| <b>Optical Axis Height (mm):</b><br>127.00                                                             |
| <b>Post Diameter (mm):</b><br>25.4                                                                     |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 224:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |