

50.8mm Clear Aperture, 30 Arcsec, Gold Retroreflector



Stock **#49-677** 3-5 DAYS

- 1 +

A\$1,304.00

ADD TO CART

Qty 1+
A\$1,304.00

Volume Pricing
Request Quote

Get Product Downloads

Beam Deviation (arcsec): 30.00
Clear Aperture CA (mm): 50.8
Coating: Protected Gold (700-2000nm)
Diameter (mm): 76.20
Exiting Wavefront Accuracy: 7.0λ

Substrate:  BOROFLOAT®
Surface Quality: 80-50
Mounting Threads: (6) ¼-20, (5) M6 x 1.0
Type: Retroreflector
Dimensional Tolerance (mm): ±1.6
Image Orientation: Left-Handed
Ray Deviation (°): 180
Wavelength Range (nm): 700 - 2000

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View