

50.0/50.8mm Optic Dia., X-Y Translating Optic Mount



5 Axes Optical Mount



Stock **#62-957** 1 In Stock

-

1

+

A\$492⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	A\$492.80 each
Qty 5-9	A\$468.16 each
Qty 10+	A\$418.88 each
Need More?	Request Quote

Product Downloads

General

Adjustable - Linear (XY)

Type:

Circular

Type of Optics:

Available in Quick Start Kit: [#17-514](#)

Note:

Physical & Mechanical Properties	
46.0	Clear Aperture CA (mm):
88.0	Outer Diameter (mm):
22.00	Thickness (mm):
±2.0 in X and Y	Travel (mm):
180	Weight (g):
Black Anodized Aluminum	Construction:

Threading & Mounting	
50.0 - 50.8	Size of Compatible Optics (mm):
15.0 (Max)	Thickness of Compatible Optics (mm):
M6 x 1.0	Compatible Post:

Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:

Product Details

- 2-Axis, 3-Axis, and 5-Axis Adjustable Mounts Available
- Options for 12.5mm (0.5"), 25mm (1"), and 50mm (2") Dia. Optics
- M6 Mounting Threads

Multi-Axis Adjustable Optic Mounts can adjust optic positioning along the X- and Y-axes, as well as through optional Z-axis and Tip/Tilt adjustment. Compact packaging allows for fine alignment adjustments without the additional use of bulkier stages. Multi-Axis Adjustable Optic Mounts are ideal for alignment adjustments in prototyping and precision laboratory benchtop optical systems. These mounts include M6 mounting threads making them compatible with our standard [Metric Stainless Steel Mounting Posts](#). A retainer ring and Delrin ring are used together to secure the optic without damaging its surface.

Technical Information

