

25mm Max. Aperture, Mounted Iris Diaphragm



50.8mm Outer Diameter, Mounted Iris Diaphragm, #53-915

Stock #53-915 3-5 DAYS



1



A\$115.20

ADD TO CART

Qty 1-4

A\$115.20

Qty 5+

A\$101.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type:

Mounted

Minimum Aperture (mm):

0.8

Maximum Aperture (mm):

25.0

Outer Diameter (mm):

50.8
Construction: Blackened Brass Housing, Stainless Steel Leaves, Stainless Steel Pin Actuators, Black Anodized Aluminum Mount
Inner Diameter (mm): 37.00
Lever Diameter (mm): 3.00
Lever Length (mm): 12.90
Mounting Threads: 1/4-20
Set Screw Thread: 6-32
Thickness (mm): 9.50

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 235: Contains SVHC(s)
