

SCHOTT KG3, 50mm Dia., 3mm Thick, Colored Glass Heat Absorbing Shortpass Filter

See More by [SCHOTT Optical Components](#)



Stock #49-090 3-5 DAYS

- 1 + **A\$128.00**

ADD TO CART

Qty 1-10

A\$128.00

Qty 11+

A\$112.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
50.00

Density (g/cm³):
2.53

Glass/Filter Number:
[SCHOTT KG3](#)

Substrate: Heat Absorbing Glass
Operating Temperature (°C): 300 Maximum
Coating: Uncoated
Index of Refraction n_d: 1.51
Surface Quality: 60-40
Transformation Temperature (°C): 581
Thickness (mm): 3.00 ±0.38
Type: IR Cut-Off Filter
Dimensional Tolerance (mm): ±0.25
Reflection Factor P_d: 0.92
Wavelength Range (nm): 300 - 2700
Bevel: Protective as needed

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View