

TECHSPEC[®] 50mm Dia. x 100mm FL, Uncoated Germanium Meniscus Lens



Stock **#87-960** 3-5 DAYS

-

1

+

A\$1,489.60

ADD TO CART

Qty 1-5
A\$1,489.60
Qty 6+
A\$1,191.68
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
50.00 +0.0/-0.1

Effective Focal Length EFL (mm):
100.00

Substrate: ☐
Germanium (Ge)

f#:
2.00

Numerical Aperture NA: 0.25
Coating: Uncoated
Type: Meniscus Lens
Wavelength Range (nm): 2000 - 14000
Back Focal Length BFL (mm): 96.49
Center Thickness CT (mm): 5.00
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <3
Clear Aperture (%): 90.00
Edge Thickness ET (mm): 3.8
Focal Length Specification Wavelength (µm): 10.6
Radius R₁ (mm): 107.03
Radius R₂ (mm): 160.46
Surface Quality: 60-40
Wavelength Range (µm): 2 - 14

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View