

TECHSPEC[®] 50mm Dia x -100mm FL, Enhanced Aluminum, Convex Mirror



Convex Mirrors

Stock #87-674 [CONTACT US](#)

-

1

+

A\$112.80

ADD TO CART

Qty 1-5
A\$112.80
Qty 6+
A\$90.40
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
50.00

Focal Length FL (mm):
-100.00

Center Thickness CT (mm):
5.00

Clear Aperture (%) 90.00
Coating: Enhanced Aluminum (450-650nm)
Coating Specification: R_{avg} >95% @450 - 650nm
Coating Type: Metal
Dimensional Tolerance (mm): +0.0/-0.1
Edge Thickness ET (mm): 3.43
Focal Length Tolerance (%): ±2
Radius R (mm): 200.0
Substrate: N-BK7
Surface Accuracy: λ/2
Surface Quality: 60-40
Thickness Tolerance (mm): ±0.1
Type: Spherical Mirror
Wavelength Range (nm): 450 - 650

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant