

50mm Diameter, Cyan Dichroic Filter



Additive and Subtractive Dichroic Color Filters

Stock #52-538 3-5 DAYS



1



A\$63.20

ADD TO CART

Qty 1-24

A\$63.20

Qty 25+

A\$55.68

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
50.00

Angle of Incidence (°):
0

Cut-Off Wavelength (nm):
590.00

Substrate:  BOROFLOAT®
Operating Temperature (°C): <100
Coating: Subtractive Color
Color: Cyan
Surface Quality: 80-50
Thickness (mm): 2.00 Nominal
Type: Dichroic Filter
Dimensional Tolerance (mm): ±0.25
Clear Aperture (%): ≥85
Coating Specification: T _{avg} >80% @ 400 - 550nm T _{avg} <1.0% @ 640 - 740nm
Cut-Off Wavelength Tolerance (µm): 0.015

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant