


50mm Diameter Narrow Elliptical Holographic Diffuser Kit



Holographic Diffusers



Stock **#56-056** [CONTACT US](#)



1



A\$1,284.00

ADD TO CART

Qty 1+

A\$1,284.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diffusing Angle (°):
0.2 x 10, 0.2 x 40, 2 x 10, 10 x 20

Diameter (mm):
50.00 ±0.1

Number of Diffusers:
4.00

Operating Temperature (°C):
-30 to +100 (Maximum of 240 Hours)

Substrate: ☐
Polycarbonate

Type:
Holographic Diffuser

Wavelength Range (nm):
400 - 700

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)
