

50mm Sq., Extended Hot Mirror



Extended Hot Mirrors

Stock **#46-388** 3-5 DAYS

- 1 +

A\$156.80

ADD TO CART

Qty 1-9

A\$156.80

Qty 10+

A\$137.92

Volume Pricing

[Request Quote](#)

Get Product Downloads

Angle of Incidence (°):
0.00

Coating:
Hot Mirror, 0°

Substrate:
BOROFLOAT®

Dimensions (mm):

50.0 x 50.0
Surface Quality: 80-50
Thickness (mm): 3.30
Thickness Tolerance (mm): ±0.2
Type: Shortpass Filter
Dimensional Tolerance (mm): ±0.5
Clear Aperture (%): ≥85
Edges: Seamed
Coating Specification: R _{avg} ≥90% @ 750 - 1150nm R _{avg} ≥80% @ 1200 - 1600nm T _{avg} ≥85% @ 425 - 675nm
Wavelength Range (nm): 425 - 1600
Surface Flatness (P-V): 4 - 6λ
Coating Type: Dielectric

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant