

50mm Travel, Motorized Linear Stage, Integrated Controller, Rotary Encoder

See More by [Zaber™](#)



#15-286, 50mm Travel, Motorized Linear Stage, Integrated Controller

Stock **#22-218** 3-5 DAYS

1

A\$3,945.60

ADD TO CART

Qty 1+

A\$3,945.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Needle Roller Bearing

Type of Drive:
Precision Lead Screw

Type:
Metric

Stage Size (mm):

45 x 188.0
Travel (mm): 50.8
Accuracy (µm): 20 (Unidirectional)
Backlash (µm): <12
Encoder: Yes
Height (mm): 21
Load Capacity (kg): 10
Manual Control/ LED Indicators: Yes
Manufacturer: Zaber Technologies Inc.
Note: Requires a 24-48 VDC power supply and either #15-295 for USB connectivity or #15-297 for RS-232 connectivity. A data cable (#15-296 or #15-299) can be used to daisy chain multiple stages together to control simultaneously.
Operating Temperature (°C): 0 - 50
Parallelism (µm): <25
Power Supply: Power Supply Required and Sold Separately. USA: #15-294 Europe: #15-294 Japan: #23-662 Korea: #33-773 China: #15-294
Repeatability (µm): <3
Resolution (µm): 0.05
Speed (mm/s): 0.00003 to 26
Type of Motor: 2-Phase Stepper
Weight (kg): 0.36
Computer Interface: USB with #15-295 RS-232 with #15-297
Maximum Operating Current (mA): 350
Encoder Type: Rotary Quadrature Encoder
Encoder Resolution: 200 CPR

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant