

TECHSPEC®

51mm Dia. Enhanced Aluminum, λ/4 Mirror



Stock #32-514

3-5 DAYS

-

1

+

A\$168.00

ADD TO CART

Qty 1-5

A\$168.00

Qty 6+

A\$134.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):

51.00

Surface Flatness (P-V):

λ/4

Substrate: ☐

BOROFLOAT®

Back Surface:

Fine Ground
Surface Quality: 60-40
Dimensional Tolerance (mm): +0.5/-0.0
Coating Specification: R _{avg} >95% @450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 85
Edges: Fine Ground
Thickness (mm): 13.00 +1.0/-0.0
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference: ☐ 0.2 J/cm ² @532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant