


TECHSPEC[®] 525nm 35mm Diameter, OD 2.0 Longpass Filter



OD 2.0 Longpass Filters

Stock **#14-665** CLEARANCE 3-5 DAYS



1



A\$63.92

ADD TO CART

Qty 1+

A\$63.92

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
35.00 ±0.1

Angle of Incidence (°):
0

Optical Density OD (Average):
≥2.0

Cut-On Wavelength (nm):
525.00

Substrate: ☐

Fused Silica (Coming 7980)	
Coating:	Traditional Coated
Rejection Wavelength (nm):	200 - 505
Surface Quality:	40-20
Thickness (mm):	5.00
Thickness Tolerance (mm):	±0.1
Transmission (%):	>85
Transmission Wavelength (nm):	545 - 2000
Type:	Longpass Filter
Clear Aperture (%):	80
Transmitted Wavefront, P-V:	λ/4
Cut-On Tolerance (%):	±2
Slope Factor (%):	3.00
Coating Specification:	Surface 1: Multi-Layer Dielectric Surface 2: MgF ₂
Wavelength Range (nm):	200 - 2000

Regulatory Compliance

RoHS:	Compliant
Certificate of Conformance:	View