

540nm CWL, 10nm FWHM, 50mm Mounted Diameter



Stock #87-002

3-5 DAYS

-

1

+

A\$710.40

ADD TO CART

Qty 1-9

A\$710.40

Qty 10+

A\$638.40

Volume Pricing

Request Quote

Get Product Downloads



Diameter (mm):

50.00 +0.0/-0.2

Angle of Incidence (°):

0

Optical Density OD (Average):

≥3.0

Clear Aperture CA (mm):

42.0
Center Wavelength CWL (nm): 540.00 ±2
Center Wavelength CWL Tolerance (nm): ±2
Full Width-Half Max FWHM (nm): 10.00 ±2
Full Width-Half Max FWHM Tolerance (nm): ±2
Minimum Transmission (%): ≥45
Operating Temperature (°C): -50 to +75
Coating: Traditional Coated
Surface Quality: 80-50
Thickness Tolerance (mm): ±0.1
Type: Bandpass Filter
Typical Applications: YFP Emission
Blocking Wavelength Range (nm): 200 - 1200
Construction: Mounted in Black Anodized Ring
Mount Thickness (mm): 7.5 ±0.1

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
