


5.5" Diameter, Plastic Optical Window



Stock **#43-926** CLEARANCE CONTACT US

- 1 +

A\$47.92

ADD TO CART

Qty 1+
A\$47.92

Volume Pricing
Request Quote

Get Product Downloads



Abbe Number (v_d):
57.00

Diameter (mm):
139.70 ±0.3

Diameter (inches):
5.5

Thickness (mm):
1.50 ±0.15

Coating:
Uncoated

Density (g/cm³): 1.320
Index of Refraction n_d: 1.501
Operating Temperature (°C): 100 Continuous, 130 for 1 hour
Substrate: Thermoset ADC (CR-39®)
Transmission (%): >90 (typical)
Type: Protective Window
Wavelength Range (nm): 400 - 1500

Regulatory Compliance

RoHS 2015: Compliant
Reach 223: Compliant
Certificate of Conformance: View