

TECHSPEC[®] 5mm Dia. Enhanced Aluminum, λ/4 Mirror



Stock #48-404 3-5 DAYS

-

1

+

A\$80.00

ADD TO CART

Qty 1-5

A\$80.00

Qty 6+

A\$64.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
5.00

Surface Flatness (P-V):
λ/4

Substrate: ☐
[BOROFLOAT[®]](#)

Back Surface:

Commercial Polish
Surface Quality: 60-40
Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >95% @450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 83
Edges: Fine Ground
Thickness (mm): 2.00 ±0.25
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference: ☐ 0.2 J/cm ² @532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View