

[See all 57 Products in Family](#)

TECHSPEC[®]

5mm Diameter, C-Mount Thin Optic Mount



Stock #54-612 4 In Stock

-

1

+

A\$95²⁰

ADD TO CART

Volume Pricing	
Qty 1-4	A\$95.20 each
Qty 5-9	A\$84.64 each
Qty 10-25	A\$78.56 each
Need More?	Request Quote

Product Downloads

General	
Fixed	Type:
Circular	Type of Optics:
Optic Mount (Fixed)	Function:

Physical & Mechanical Properties

5.6	Extension Length (mm):
Black Anodized Aluminum (6061 T6)	Construction:
9.6	Total Length (mm):
30.0	Outer Diameter (mm):
3.80	Clear Aperture CA (mm):
3.0	Max. Thickness of Compatible Optics (mm):
1.0	Min. Thickness of Compatible Optics (mm):

Threading & Mounting

5.0	Diameter of Compatible Optics (mm):
C-Mount	Thread Type:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

- Mounts for Simple Lenses, Achromats, Filters, or Reticles
 - Designed to Integrate with Any C, S, or T-Mount Components
 - Optic is Held in Place with Included Retaining Ring
- TECHSPEC® C, S, and T-Mount Circular Optic Mounts are designed to mount a variety of circular optical components into C, S, or T-Mount compatible systems. An included threaded retainer ring, designed to accept a standard spanner wrench, securely holds the optical component. These circular optic mounts are compatible with a wide variety of Edmund Optics optomechanical components utilizing C, S, or T-Mount threads, such as [extension tubes](#) and [kinematic mounts](#). TECHSPEC® C, S, and T-Mount Circular Optic Mounts are threaded for 1" x 32TPI, M12 x 0.5, or M42 x 0.75 mounting, with 30mm, 16mm, and 48mm outer diameters, respectively. These mounts are ideal for creating and personalization of a diverse range of optical systems.
- Note:** [#56-353](#), [#56-354](#), [#52-933](#), and [#52-292](#) are all 3-part assemblies

Technical Information

